

Standard size

2 mL Columns (Polypropylen - PP)

Order N°: AC-141-AL

- Empty columns
- Bag of 100 columns, including 100 frits¹ (polyethylene - PE) and 100 caps-(PP)
- Luer² connection at column outlet
- Column outlet sealed with breakable tip

Also available prepacked with resin³.

Dimensions :

Internal diameter: 7 mm

Filling height of resin : > 39 mm

External diameter of column outlet (Luer): 4 mm

Internal diameter of column outlet (Luer): ~2 mm



Accessories for 2 mL columns

1/ 20 mL funnel (PP)

Order N°: AC-120, bag of 20

Order N°: Réf : AC-121, bag of 100

Dimensions :

Upper diameter : 25 mm

Height : 78 mm

Volume : up to 25 mL



2/ Column closure caps

Order N°: AC-131-C, bag of 50

For capping 2 mL standard columns for storage.

Works also for 5 mL and 20 mL columns



¹ Frits : pore size = 30µm

² Luer : standard type connection

³ Available with the following resins : AC, CL, LN, NI, PB, RE, SR, TEVA, TRU, UTEVA in boxes of :

- 20 units (C20)

- 50 units (C50)

- 200 units (C200 corresponding to 4xC50)

TRISKEM INTERNATIONAL

Parc de Lormandière Bât. C – Rue Maryse Bastié – Campus de Ker Lann – 35170 Bruz – France

Tel +33 (0)2.99.05.00.09 – Fax +33 (0)2.99.05.07.27 – www.triskem-international.com – email : contact@triskem.fr

SAS au capital de 40.000 euros – SIRET 493 848 972 00011 – APE2059Z – TVA intra communautaire FR65 493 848 972



PRODUCT SHEET COLUMNS

3/ Rack 12 positions - Plexiglas

Order N°: **AC-104**

Numerated positions (1 to 12)

Racks can be staggered for sequential separations

Dimensions :


Height : 128 mm

Length : 475 mm

Width : 120 mm

Height beneath single rack : 122 mm

Height between 2 staggered racks : 115 mm



4/ Rack 15 positions - acrylic


Order N°: **AC-103**

Dimensions :

Height : 160 mm

Length : 240 mm

Width : 115 mm



PRODUCT SHEET COLUMNS

5mL Columns (PP)

Order N°: **AC-50E-5M**

- Only available as empty columns
- Bag of 50 columns, including 50 frits (PE) and 50 caps (PP)
- Luer² connection at column outlet
- Column outlet closed with cap

Dimensions :

Internal diameter : 9-9,5 mm

Filling height of resin : up to 8 cm

External diameter of column outlet (Luer): 4 mm

Internal diameter of column outlet (Luer): ~2 mm



Accessories for 20 mL columns

1/ 250 mL funnel (PP)

Order N°: **AC-20X-20M**, Bag of 20

Dimensions :

Upper diameter : 63 mm

Height : 150 mm

Volume : up to 250 mL



2/ Acrylic racks

Order N°: **AC-103** or

AC-12M-RACK with adaptators of conic caoutchouc joint type (\varnothing ext. inf./sup. 22/36 mm and \varnothing int. 15 mm)

See

“4/” of accessories for 2mL columns and/or

“1/” of accessories for 20mL columns

PRODUCT SHEET COLUMNS

20mL Columns (PP)

Order N°: **AC-20E-20M**

- Only available as empty columns
- Bag of 20 columns, including 20 frits (PE) and 20 caps (PP)
- Luer² connection at column outlet
- Column outlet closed with red cap

Dimensions :

Internal diameter : 15 mm

Filling height of resin : up to 10 cm

External diameter of column outlet (Luer): 4 mm

Internal diameter of column outlet (Luer): ~1.5 mm



Accessories for 20 mL columns

1/ 250 mL funnel (PP)

Order N°: **AC-20X-20M**, Bag of 20

Dimensions :

Upper diameter : 63 mm

Height : 150 mm

Volume : up to 250 mL



2/ Rack 12 positions - acrylic

Order N°: **AC-20M-RACK**

Dimensions :

Height : 235 mm

Length : 460 mm

Width : 153 mm

Ø : 25 mm

Distance between each position (from side to side) :
50 mm





PRODUCT SHEET COLUMNS

Columns available on request : 5, 8 et 10 mL

Pre-packed columns (PP) in boxes of 20 units, available for SR, TEVA, TRU and UTEVA resin :

Order N°:

SR5-C20-A, SR8-C20-A, SR10-C20-A

TE5-C20-A, TE8-C20-A, TE10-C20-A

TR5-C20-A, TR8-C20-A, TR10-C20-A

UT5-C20-A, UT8-C20-A, UT10-C20-A

- Luer² connection at column outlet
- Column outlet sealed with breakable tip

Dimensions :

Internal diameter : 14 mm

Volumes : 5 mL resin
8 mL resin
10 mL resin

